
XY Table and Linear Modules

Overview

The XY table and linear modules are the basic parts of various CNC and electronic manufacturing equipments. They are also general purpose platform for scientific research, application development and educational experiments. The Googol GXY Series XY tables and Linear Modules, which are tailored made for manufacturers and technical institutes, is based on modularized design and industrial manufacturing standard, and is widely used in various areas of CNC and precision position control equipment research and development such as welding, dispenser, bonding, drilling, packing etc. They are also widely used in universities and colleges for advanced research and teaching in the area of mechantronics, computer control system, mechanical engineering and CNC technology, etc.



Control & Experiment Software Interface



ST Comm	nder DO													- (2) 🔀
					m - 1 NT									
	_	6 ¥ U	892	10 2 4		_	8.5828					13	\$\$\$.5.5.5 · \$\$	
W187.407	_	为(15-18 P);				ste	wi				20530	JE 1171	后有任动完成/无關於指令	
#etc	₩û	₩2 <u>%</u>			102 NO2	4 183		୍ୟର ଜ≉ର ଏକ+ି ିରେକ		A.51517K	* B97		100-101-101-10-00-00-00-00-00-00-00-00-0	*
0.0	0.0	0.0	00	00 0	0 03				· [• •			100-4410-7	2
*1	81		*1	81 - A		- 168.2	17588	\$1 92 (95: 200		0000 ±	e:812 :	0.000	单位和密度也更大	÷
						-						· · · · ·	這些問題解释書	×
XHX .	895	第16位			N HE MINE	010	フ重明	1641: 2000				0.000	异氧时目结体无计	*
0.0	00	0.0	00	00 0	0 03	0.30	24四秋	205 A C 3.000		0000		0.000	之间面补收应	*
* 1	81	•	81	81 - A	a 🛛 🔬		201.200.WR	-17.5.: [1000		81F : 1	→ 42:	0.000	向第十点机中的运动分 約半点机站开始间里	2
						-		立時重新状态					100万1000万里拉来	×
SALE SALE	6.711-254	+: 76.1	0,(E##+);				目前目の方式	* HEYGERA	0 62Ex	VZBALK	- Ettinz	1212.0	2656808	
						0.10	图系均乐单位)	×:0.000	v: 0.00	2: FMH		0.000	ret 0.000	
g: 1 2	1 3 4	6.6	7 8 6	9 10 11	12 13 14 11	0 V2	観測対点半日)	26-592	STATISTIC P	6 7110000		8.67.6 B	·# 0.000	
XX	< x >	< x x	XXX	× × x	x x x >	0.28	田利(竹水半荘)						246 0.000	
1 1000 000						_	XTEOROM	######	110010100	2 平田協()	CA I MO	EKG9	0.000	
P		10					02595		- 9884 -				DOGOLITEX	Nor
e Filititit	100/1 m	•		-FUB.X/R	* BORBLO				0155					301
			28490	国際の設計を設	C 王仪面明		E Run	* 08/20	Cinvetia	C NTRI	1983675		-	
15794EE	0		C OT FES		C 24200		Prose				: 0.00			
1 120111	0		× 18999	CREATE ST	0 1568.0			0.685/243			: 0.308	O NO FORMA		
Rightens Fernitessa	e 1: 0		Time Hill?	indo h672	NEWS:		C 216	0 955210				A INT PR		
1277 6783					-1907- I	- man/1015						いた形正規		
A BERSHOLD		79	-	o dotte sizeet	8月1日 电子齿轮		01	标清等				D #883	a	
Aziema:	52	252	2015	0	mana: 0		平正教育							
12.4.4					mark i		74985							
-	1: 4	24	36.0X :	0				ENTORIA		x+	Ŷ+			
ROPERT:							0.95998	WEIGHT HERE	ERCentral	X-	Y-			
1203172	0 F			4.46W		位最易分	* 14346	5 -	sə •	Ŷ	×	w w		
	-	201	10925	4982	0.23.967.20	2月96			使同意					4
unrest.	24		23.701	MRDE3	5.039	7371	© 12E PK	M4 01	P1-1P1			E 2011		

Main Features

• Modularized Design

- ✓ Modularized design of mechanical body, users are able to configure different motors and axis number to set up their individual application system or experimental platform.
- ✓ Experiment software is developed based on the modularization principle. Experiments and application modules are configurable according to the real application system.

• Industrial Standard Design and Manufacturing

- ✓ Adopt high-precision ball screw and roller slide way
- ✓ All-in-one aluminium extruded sections base
- ✓ Manufactured in ISO9002 system

• Open Architecture

- ✓ Open control system based on PC and DSP motion controller.
- ✓ DOS and DLL function libraries applicable in Windows environment (such as VC, VB and Dephi)
- ✓ Open source XY table experiment software.

- ✓ Detailed experiment textbook, covering every design and realization aspects of the mechatronic system. User can select relevant contents freely to meet the teaching and experiment needs for various courses.
- Creativity
- ✓ Configurable experimental platform.
- ✓ Development of application systems to meet the industry needs.

Control System and Software Features

- Realize single-axis motor various motion modes control (S-curve, T-curve, speed mode, electrical gear mode) and 2-axis interpolation or synchronized control.
- Abundant visualization graphical interfaces, display the motion parameter (velocity, acceleration and positon) curves and the simulation and actual motion trajectory of the platform in real time.
- According to the educational experiments requirement of individual user, the experimental modules can be flexibly configured and thus to facilitates the educational experiments and research works greatly.

Experiment and Research Contents

Basic Experiments

- ✓ Motion control system basic experiment
- ✓ Motion control system PID control
- ✓ Motor and driver experiments
- ✓ Single-axis motion planning
- ✓ 2D interpolation principle and application
- ✓ XY table motion control
- ✓ NC code programming
- Research Experiments
 - ✓ 2D motion control application system development
 - ✓ 2D trajectory interpolation algorithm research
 - ✓ NC code interpreter development and research
 - ✓ XY table high-accuracy tracking control

Technical Specifications

a. XY Table (Unit: mm)

Model	Distance route		Base size			Table size			Load	Resetting	Setting
	Х	Y	L	W	Н	L	W	Н	(N)	accuracy	accuracy
GXY-2020	200	200	450	450	184	240	254	15	600	±0.03	0.05
GXY-3030	300	300	550	550	184	240	254	15	000	±0.03	0.05

b. Linear Module (Unit: mm)

Model	Distance	Length	Base size		Table size		Load	Resetting	Setting
Widdei	route		L	W	L	W	(N)	accuracy	accuracy
GX-200	200	~578	450	250	240	254	1000	±0.03	0.05
GX-300	300	~678	550	250	240	254	1000		

- The above platforms are all equipped with positive and negative limit switches. Penholder or drawing device are optional for teaching use.
- Technical specifications and structure of special purpose 3D NC platform can be customized.

Ordering Guide

Model Number	Model Name	Description				
GXY2020GT4B GXY3030GT4B	2D step XY table	 P1-grade accuracy mechanical body GT-400-SG motion controller + Two-axis step electrical control module Automatic penholder Experiment software in Windows 				
GXY2020VD4B GXY3030VD4B	2D DC servo XY table (Close-loop)	 P1-grade accuracy mechanical body GT-400-SV motion controller + Two-axis servo electrical control module Automatic penholder Experiment software in Windows P1-grade accuracy mechanical body GT-400-SG motion controller + Two-axis 				
GXY2020GP4B GXY3030GP4B	2D AC servo XY table (Open-loop)	 servo electrical control mode Automatic penholder Experiment software in Windows P1-grade accuracy mechanical body 				
GXY2020VP4B GXY3030VP4B	2D AC servo XY table (Close-loop)	 GT-400-SV motion controller + Two-axis servo electrical control module Automatic penholder Experiment software in Windows 				

Please contact us to order other model of XY table and linear modules.

GOOGOL TECHNOLOGY (HONG KONG) LIMITED RM 3639, ANNEX BLDG, HKUST Clear Water Bay, Kln, HK Tel: +852 2358 1033 Fax: +852 2719 8399 Email: <u>Sales@googoltech.com</u> (Products Enquiry) Website: <u>http://www.googoltech.com.hk</u> GOOGOL TECHNOLOGY (SHENZHEN) LIMITED RM W211, IER BUILDING, SOUTH AREA SHENZHEN HI-TECH INDUSTRIAL PARK TEL: +0755 2697 0817 FAX: +0755 2697 0846 EMAIL: GOOGOL@GOOGOLTECH.COM (PRODUCTS ENQUIRY)

WEBSITE: <u>http://www.googoltech.com.cn</u>